

# MIH<sup>®</sup> VMJ PV Cell

## Cell-Module

## Datasheet



### Key Features:

- High efficiency Si-based MIH<sup>®</sup> VMJ PV cell
- Efficiency with 975nm laser up to 34% at 15 W/cm<sup>2</sup>
- High voltage density: 30V standard 10mm x 10mm cells
- High temperature durability (up to 120°C operation)
- Optimal efficiency with 9xxnm lasers
- High thermal conductivity copper substrate

### Applications:

- Unmanned Aerial Vehicles
- Remote sensor charging
- Wireless Power Transmission

### Product Description

MH GoPower (“MHGP”) offers the only photovoltaic receiver product line capable of delivering a wide range of power and voltage outputs. Power output levels range from tens of milliwatts to hundreds of watts, while output voltage levels are possible from 4 volts to over 30 volts (higher voltages possible by wiring VMJ PV cells in series). MHGP’s Cell-Module is constructed by paralleling 25 standard 10mm x 10mm cells together. The Cell-Module product line operates most efficiently with wavelengths in the range of 900 nm to 1,000 nm.

The YCH-H300M is MHGP’s standard Cell-Module product offering, suitable for applications requiring power up to 300 watts when active cooling available. Note: higher power output is also possible with good thermal management (performance of the VMJ PV Cell-Module will drop ~3% for every 10°C increase in temperature).

Target applications include dense array PV receivers for laser power beaming (including powering UAVs, aerospace applications, and remote ground based sensors), and for high power, power over fiber applications. Features of target applications include need for remote power delivery, or high voltage isolation, or need to operate in high voltage or high EMI environments.




## Electrical Characteristics \*

Part Number	Length (mm)	Width (mm)	Height (mm)	Input Power (W)	Power Density (W/cm <sup>2</sup> )	Vmax (V)	I <sub>max</sub> (A)	P <sub>max</sub> (W)	Efficiency (%)
YCH-H300M	131.0	58.2	16.0	189	7	30.4	2.1	65.1	34.4%
				403	15	29.1	4.7	136.6	33.9%
				623	23	28.0	7.0	195.4	31.4%
				807	30	27.3	8.8	239.6	29.7%
				1023	38	26.6	10.5	279.2	27.3%

\* Typical converter performance of YCH-H300M

\* Tested with 975 nm laser source and 7 L/min, 15°C cooling water

\* Efficiency will vary depending on level of light uniformity, as well as Cell-Module temperature



## Customization Options


The following Cell-Array parameters can be customized upon request.

- VMJ PV cell Size
- Substrate Size
- Array Configuration (number of rows and columns)
- Output Configuration (series or parallel wiring)
- Electrical Connector output

## Recommended Testing Guidance

Our Cell-Arrays allow customers to quickly test the performance of our VMJ PV cells in dense array applications. Our standard Cell-Arrays are designed for indoor, laboratory testing. It is not recommended that the Cell-Arrays be tested in outdoor applications subject to high humidity and condensation. Customization for outdoor applications and testing is available upon request.

## Mechanical Dimensions



Net Weight: 670g